

Kellogg 530 and 550 Select-O-Phone Network Schematic and wiring information

37-13-D 3-wire Dial White/Blue/Green

P-75335-2 Network same terminal designations as a 425 Network

8A DC ringer – correct for the SOP

Ringer Pushbutton 3 terminal Common/Make/Make

Handset - normal G3 with red/black transmitter white/white receiver

Hookswitch – standard 500 set hookswitch

Wiring

-Line Cord -

Select-O-Phone “L” Lead Green wire on network terminal L2

Select-O-Phone “S” Lead Red wire on network terminal L1

Select-O-Phone “C” Lead White or Yellow wire on network terminal K

- Ringer -

Ringer Black to L2

Ringer Red to G

- Pushbutton-

Pushbutton Cloth Red to network terminal R

Pushbutton Slate/Green to network terminal GN

Pushbutton Slate/Red to network terminal L2

- Handset-

Red to network terminal RR

Black to network terminal B

White to network terminal R

White to network terminal GN

- Dial-

Blue to network terminal K common - NO but closed at windup to pulse contact

Green to network terminal F on network - NC pulse contact

White to network terminal R - NC at rest

-Hook Switch-

Slate to network terminal G NC contact set 1

Slate-Yellow to network terminal L1 Common contact set 1

Slate-Brown to network terminal C NO contact set 1

Slate-White to network terminal B NO contact set 2

Slate-Green to network terminal L2 Common set 2

Slate-Red to network terminal GN NO contact set 3 - receiver mute

Slate-Black to network terminal R Common contact set 3 - receiver mute

P-75335-2 Network

